






#### **Typical Ultrapure Water Treatment Steps**



#### **Monitoring Points and Key Parameters**

1 City Water

2 Multimedia Filtration

3 Activated Carbon Prefilter

4 Reverse Osmosis

5 TOC Reduction

6 Membrane Degasifier

7 Ozone Destructor

8 Mixed-Bed Primary

9 TOC Reduction

10 Mixed-Bed Polishing

pH, TOC, TURB FCL, TURB

DISF, FCL, TURB

pH, ORP, Conductivity

TOC

 $O_2$ 

 $O_3$ 

RES, Na, SiO<sub>2</sub>

TOC

Na, RES, SiO<sub>2</sub>, TOC

DISF = Disinfectant

FCL = Free Chlorine

Na = Sodium

O<sub>3</sub> = Dissolved Ozone

O<sub>2</sub> = Dissolved Oxygen

ORP = Oxidation/Reduction Potential

pH = pH Value

RES = Resistivity

SC = Specific Conductivity

SiO<sub>2</sub> = Silica

TOC = Total Organic Carbon

TURB = Turbidity

#### Conductivity (Specific)/Resistivity





### Disinfectants





#### **AMI Powercon S**

Complete monitoring system for the automatic, continuous measurement of the specific (total) conductivity

- Complete system with dedicated transmitter, high-precision conductivity sensor, flow cell with needle valve and digital sample flow meter
- Two-electrode Titanium conductivity sensor with high-precision cell constant and integrated Pt1000 temperature probe.
- Quick sensor release with patented slot-lock design
- Factory tested and ready for use

Specific Conductivity 0.055 µS/cm-30 mS/cm

#### **AMI Rescon**

Online monitoring for specific resistivity/specific conductivity according to USP <645>

- In-situ verification with ultra-high precision resistor
- High temperature flow cell with integrated sensor for flow measurement
- Automatic selectable temperature compensation for different sample conditions
- Automatic measurement range switching
- Flow rates from 70-100 l/hr

Resistivity 0.01-18.24 MΩ Specific Conductivity 0.055-1000 uS/cm

#### **AMI Trides**

Amperometric measurement and control system for disinfectant concentrations

- Reagent-free low operating costs with durable, membranefree sensor design
- Low maintenance, high zero point stability, high longevity with automatic sensor cleaning
- Reliable measurements with integrated monitoring of redox potential and/or pH value (incl. compensation)

#### **AMI Codes-II**

Photometric measurement for disinfectant concentrations according to AWWA 4500-CI G/EN ISO 7393-2

- Insensitive to crossmeasurements, chemicals and ion interferences
- Automatic zero-value calibration prior to each measurement for high accuracy and reproducibility
- Reduced maintenance with optional cleaning module and high tolerance against fouling

Free Chlorine
0-5 ppm
Chlorine Dioxide
0-3 ppm
Ozone
0-1 ppm

Free Chlorine
0-5 ppm
Chlorine Dioxide
0-6 ppm
Ozone
0-1 ppm

#### **Dissolved Oxygen**



**AMI Oxytrace** 

Amperometric measure-

ment of trace dissolved

oxygen concentrations



### **AMI Oxytrace QED**

Measurement of dissolved oxygen

- Sensor with 3 electrode set-up (gold cathode, silver anode and silver guard) and temperature sensor. Faster initial response time after maintenance due to silver guard
- Automatic temperature and air pressure compensation for simple calibration using ambient air
- Automatic surveillance of electrolyte
- Available on a compact panel (280 x180 mm)

Dissolved Oxygen 0-20 ppm Saturation 0-200%

including integrated auto-verification

- Faraday electrode setup for automatic or manual verification by electrochemically generated oxygen concentration in the ppb range
- Monitoring of electrolyte and membrane integrity through faraday verification
- Easy to handle membrane and electrolyte exchange, sensor cap for up to 24 months of operation
- Available on a compact panel (400 x 420 mm)

Dissolved Oxygen 0-20 ppm Saturation 0-200%

#### pH/Redox Potential



#### **AMI-II pH-Redox QV-Flow**

Potentiometric determination of pH value or redox potential for low conductivity samples

- pH or redox electrode with liquid electrolyte reference sensors, and Pt1000 temperature probe
- Automatic temperature compensations models for pH measurement, for high purity water
- Straightforward calibration procedure without sensor disassembling
- Economical operation of the instrument due to refillable liquid electrolyte

pH Range pH 1-13 Redox Potential (ORP) -1500 to 1500 mV

#### Silica



#### **AMI Silitrace**

Determination of trace concentrations of silica

- Detection limit of 0.5 ppb
- Automatic sample heating and regulated reaction time features for highest precision
- Automatic zero verification (daily)
- Programmable, automatic calibration
- Optional 2nd sample channel, or automatic sample sequencer; up to 6 sample streams

Silica 0-1000 ppb



#### **AMI Silitrace Ultra**

Colorimetric measurement of trace amounts of silica

- Real time and gap free monitoring through Swan Plug Flow System
- Heated photometer for low sample temperatures
- Programmable verification and calibration
- Integrated constant-temperature reaction chamber

Silica 0.005-25 ppb

#### **Sodium**



#### **AMI Soditrace**

Measurement of trace sodium concentration

- Lowest available detection limit for sodium ion concentrations of 0.001 ppb
- pH controlled alkalization reagent addition for diisopropylamine to a pH 12, via maintenance-free air pump
- Programmable automatic threepoint known addition calibration in ppb-range (detection limit for sodium remains: 0.001 ppb)
- Programmable automatic regeneration of sodium electrode

Sodium 0.001-10000 ppb



#### **AMI Sodium A**

Dissolved sodium measurement for samples with pH≥2 and pH<8

- Detection limit of 0.1 ppb
- pH controlled alkalization reagent addition for diisopropylamine with maintenance-free air pump
- Optional 2nd sample channel, or automatic sample sequencer; up to 6 sample streams

Sodium 0-10000 ppb

#### **Total Organic Carbon**





#### **AMI-II LineTOC Compact**

Online monitoring for Total Organic Carbon (TOC) according to USP <643> and EP 2.2.44

- Reagent-free operation for fast trend identification without costly lab analysis
- Automatic performance verification (SST)
- Integrated grab sample function
- Optimized cost of ownership: auto-shutoff and safe ramp-up depending on sample flow to protect equipment
- Optional stainless-steel cover for extra protection of equipment and easy cleaning

Total Organic Carbon (TOC) 0-1000 ppb

#### **Turbidity**



#### **AMI Turbitrace**

Nephelometric system for low level turbidity measurement, according to ISO 7027 (EN 27027, DIN 38404)

- Programmable automatic zero point measurement for drift compensation
- Fast response time (T90<15sec at 10 l/h)
- Valve and connector for calibration according to ISO 7027
- Pressure tight sample system avoids outgasing of sample

Turbidity
0-100 FNU/NTU



#### **AMI Turbiwell**

Contact-free turbidity measurement; approved alternative method to US EPA 180.1/ISO 7027

- Heated optics prevent measurement errors and condensation
- Applicable for flocculation control (coagulant dosing)
- Automatic measurement chamber flushing; trouble-free operation without manual intervention
- Fast and easy verification with primary and secondary standard
- Optional deltaT flow meter; optional sample degasser to avoid the formation of interfering bubbles in the sample

Turbidity (EPA) 0-100 FNU/NTU Turbidity (ISO) 0-200 FNU/NTU

#### **Portable Instruments**



#### **AMI Inspector**


Portable quality assurance (verification) of existing online measurements. Available for conductivity, hydrogen, oxygen and pH measurements

- USB data logger interface for lifelong data storage at a selectable interval
- Rechargeable battery for more than 24 hours of stand-alone operation
- Recertification by Swan possible

Conductivity
0.055-1000 µS/cm
Hydrogen
0.1-800 ppm
0-50 % Saturation
Dissolved Oxygen
0-20 ppm
0-200 % Saturation
pH Range
pH 1-12

#### **Options**





#### **AMI Sample Sequencer**

Complete system for the automatic, continuous multiplexing of up to six sample streams to one process analyzer

- Complete system including control unit, back pressure regulator and needle-valve for each stream, and flow measurement
- Signal outputs for indication of active sample stream and flow alarm
- Optional module to use conjointly with these monitoring systems:
  - AMI Sodium P
  - AMI Sodium A
  - AMI Silica
  - AMI Silitrace

#### **Cleaning Module**

O EST

Reliable accurate measurements ensured by counteracting biogrowth inside the flow cell and photometer

- Automatic cleaning with addition of one or two cleaning solutions (e.g. 2.5% hypochlorite solution and/or diluted sulfuric acid 2.5%)
- Custom-programmable cleaning interval
- Automatic reagent level monitoring
- Optional module to use conjointly with these monitoring systems:
  - AMI Codes-II

#### **Swan AMI Monitor Concept**



Swan instruments are delivered as fully functional, ready-to-use instruments. This ensures easy system integration as well as user-friendly operation and maintainability.

Highest standards in development and production assure the instrument quality expected by our customers.



#### **Full System Integration**

- Complete panel-mounted systems with fluidics connections preconfigured for quick start up
- Various communication possibilities with Profibus, Modbus, HART-Protocol, USB-interface and analog output
- Simple process engineering with regulation functions (P, PI, PID or PD), relay or analog output

#### **Easy Maintenance**

- Uniform menu navigation for easy operation and maintenance – one platform for all instruments
- Clearly arranged setup of instruments, good accessibility of all components for efficient operation and maintenance
- Self-explanatory maintenance procedures can be easily performed by the operating company

#### **Highest Quality Assurance**

- Every analyzer undergoes rigorous quality checks and precise factory calibration prior to delivery
- Automatic instrument alarms and self-diagnostic such as reagent level and sensor functions for validated results
- Integrated sample flow control for measurement check available for all analyzers

#### **Swan Customers Service and Maintenance**

## Expert Training and Maintenance

- Flexible on-demand or scheduled maintenance services
- Expert re-calibration and re-certification options
- Comprehensive product trainings to boost your team's expertise

#### **After-Sales Support**

- Skilled engineers ready to assist with any technical request
- Scheduled maintenance visits to prevent downtime
- Fast, reliable service on-site or remote

# Genuine Parts and Repairs

- On-demand service including delivery of spare parts and consumables
- Authentic Swan sensors, reagents, and components
- Convenient send-in repairs at regional Swan workshops





